



M55267030



## T and X piece, LF/FB 60150, grey

### Technical properties

#### Configuration

Antibacterial treatment No

#### Compatibility

Product compatibility LF, LFF, FB

#### Dimensions

Trunking height 61 mm

Trunking width 150 mm

Measure a 250 mm

#### Cover, door

Lid with softlip -

#### Materials

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Accessories included

Accessory configuration Moulded

#### Standards

European directive RoHS voluntary compliance

#### Safety

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...65 °C