



M55317030



Internal corner, LF/FB 60190, grey

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Trunking width 190 mm

Measure a 130 mm

Cover, door

Lid with softlip -

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C