



M55319010



**Internal corner, LF/FB 60190, pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility LF, LFF, FB

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 61 mm

Trunking width 190 mm

Measure a 130 mm

**Cover, door**

Lid with softlip -

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C

**temperatur**

Ambient temperature -5...65 °C