



M55337030



End cap, LF/FB 60190, grey

Technical properties

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

Compatibility

| | |
|-----------------------|-------|
| Product compatibility | LF/FB |
|-----------------------|-------|

Connectivity

| | |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

Dimensions

| | |
|-----------------|-------|
| Trunking height | 61 mm |
|-----------------|-------|

| | |
|----------------|--------|
| Trunking width | 190 mm |
|----------------|--------|

Materials

| | |
|--------|------------|
| Colour | stone grey |
|--------|------------|

| | |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

Standards

| | |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

Safety

| | |
|-----------------|------|
| Impact strength | IK07 |
|-----------------|------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|