



M55367030



## T and X piece, LF/FB 60190, grey

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	LF, LFF, FB
-----------------------	-------------

#### Dimensions

Trunking height	61 mm
Trunking width	190 mm
Measure a	290 mm

#### Cover, door

Lid with softlip	-
------------------	---

#### Materials

Colour	stone grey
Material	PVC
Material group	plastic
Type of surface treatment	untreated

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

#### temperatur

Ambient temperature	-5...65 °C
---------------------	------------