



M55419010



Internal corner, LF/FB 60230, pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF, FB

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Trunking width 230 mm

Measure a 130 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C