



M55467030



T and X piece, LF/FB 60190, grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LF, LFF, FB
-----------------------	-------------

Dimensions

Trunking height	61 mm
-----------------	-------

Trunking width	230 mm
----------------	--------

Measure a	290 mm
-----------	--------

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	stone grey
--------	------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------