



M58057030



Flat corner, LF 40040, grey

Technical properties

Architecture

Fixing mode Hold in position thanks to lid

Configuration

Antibacterial treatment No

Dimensions

Trunking height 40 mm

Trunking width 40 mm

Measure a 68 mm

Cover, door

Lid with softlip -

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...65 °C