



M58067030



**T and X piece, LF 40040, grey**

**Technical properties**

**Architecture**

Fixing mode Hold in position thanks to lid

**Configuration**

Antibacterial treatment No

**Dimensions**

Trunking height 40 mm

Trunking width 40 mm

Measure a 170 mm

**Cover, door**

Lid with softlip -

**Materials**

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Accessories included**

Accessory configuration Moulded

**Standards**

Approvals EN50085-2-1

European directive RoHs voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C

**temperatur**

Ambient temperature -5...65 °C