



M58337030



End cap, FB 99230, grey

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	100 mm
-----------------	--------

Trunking width	230 mm
----------------	--------

Materials

Colour	stone grey
--------	------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
---------------------	------

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------