



M59659010



**Flat corner, LF 30030, pure white**

**Technical properties**

**Configuration**

|                         |    |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

**Compatibility**

|                       |         |
|-----------------------|---------|
| Product compatibility | LF, LFF |
|-----------------------|---------|

**Dimensions**

|                 |       |
|-----------------|-------|
| Trunking height | 30 mm |
| Trunking width  | 30 mm |
| Measure a       | 60 mm |

**Cover, door**

|                  |   |
|------------------|---|
| Lid with softlip | - |
|------------------|---|

**Materials**

|                           |                       |
|---------------------------|-----------------------|
| RAL colour                | RAL 9010 - Pure white |
| Material                  | PVC                   |
| Type of surface treatment | untreated             |

**Installation, mounting**

|               |                       |
|---------------|-----------------------|
| Base punching | Without base punching |
|---------------|-----------------------|

**Settings**

|             |      |
|-------------|------|
| Angle range | 90 ° |
|-------------|------|

**Accessories included**

|                         |         |
|-------------------------|---------|
| Accessory configuration | Moulded |
|-------------------------|---------|

**Safety**

|                 |      |
|-----------------|------|
| REACH conform   | No   |
| RoHS conform    | Yes  |
| Halogen free    | No   |
| Impact strength | IK07 |

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|

**temperatur**

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...65 °C |
|---------------------|------------|