



M61138014

End cap, LF 15015, brown

Technical properties

Architecture

Fixing mode Clamping and screwable

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 15 mm

Trunking width 15 mm

Materials

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHs voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...65 °C