



M612390101



endcap halogen free for trunking system LFxxx 20x20mm pure white

Technical properties

Architecture

Fixing mode Clamping and screwable

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 20 mm

Trunking width 19 mm

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

Protection index IP IP30

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...65 °C