




M61429010



**External corner, LF 20035/36, pure white**

**Technical properties**

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

Product compatibility	LF, LFF
-----------------------	---------

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	20 mm
Trunking width	33 mm
Measure a	14 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

**Use conditions**

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...65 °C