



M61468014

T and X piece, LF 20035/36, brown

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	20 mm
Trunking width	33 mm
Measure a	92 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------