




M61829010



external corner halogen free for trunking system LFxxx 30x45mm pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LF, LFF
-----------------------	---------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	30 mm
Trunking width	45 mm
Measure a	30 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature

-5...90 °C

temperatur

Ambient temperature

-5...65 °C