



M61857030



**flat angle halogen free for trunking system LFxxx 30x45mm grey**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility LF, LFF

**Dimensions**

Trunking height 30 mm

Trunking width 45 mm

Measure a 60 mm

**Cover, door**

Lid with softlip -

**Materials**

Colour stone grey

Material PC-ABS

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C

**temperatur**

Ambient temperature -5...65 °C