



M61859010



flat angle halogen free for trunking system LFxxx 30x45mm pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF, LFF

Dimensions

Trunking height 30 mm

Trunking width 45 mm

Measure a 60 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material PC-ABS

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Safety

Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

Ambient temperature -5...65 °C