



M66519010



Technical properties

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 30 mm

Trunking width 45 mm

Measure a 60 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

temperatur

Ambient temperature -30...90 °C