



M66519010



Technical properties

Architecture

Fixing mode	Hold in position thanks to lid
-------------	--------------------------------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	30 mm
Trunking width	45 mm
Measure a	60 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------