



M66639010



endcap halogen free for trunking system LFxxx 40x60mm pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 40 mm

Trunking width 60 mm

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

Ambient temperature -30...90 °C