



M66659010



flat angle halogen free for trunking system LFxxx 40x60mm pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	40 mm
Trunking width	60 mm
Measure a	85 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Safety

REACH conform	Yes
RoHS conform	Yes
Impact strength	IK07

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------