



M66669010



T-piece halogen free for LFxxx 40x60mm pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	40 mm
Trunking width	60 mm
Measure a	170 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------