



M66859010



**flat angle halogen free for trunking system LFxxx 60x110mm pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Dimensions**

Trunking height 60 mm

Trunking width 110 mm

Measure a 140 mm

**Cover, door**

Lid with softlip -

**Materials**

RAL colour RAL 9010 - Pure white

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -5...90 °C

**temperatur**

Ambient temperature -30...90 °C