



M66869010



T-piece halogen free for LFxxx 60x110mm pure white

Technical properties

Configuration

Antibacterial treatment No

Dimensions

Trunking height 60 mm

Trunking width 110 mm

Measure a 190 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

Ambient temperature -30...90 °C