



M66939010



Technical properties

Architecture

Fixing mode Clamping and screwable

Compatibility

Product compatibility LF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 60 mm

Trunking width 150 mm

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHS voluntary compliance

temperatur

Ambient temperature -30...90 °C