



M66959010



Technical properties

Architecture

Fixing mode Hold in position thanks to lid

Dimensions

Trunking height 60 mm

Trunking width 150 mm

Measure a 180 mm

Cover, door

Lid with softlip -

Materials

Colour pure white

Material PC-ABS

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

temperatur

Ambient temperature -30...90 °C