




MZ205



Under voltage release 48V DC

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	0 V
------------------------------	-----

Voltage

Rated insulation voltage	4000 V
DC control voltage	48 V
Command voltage AC	0 V
Rated operational voltage in DC	48 V

Electric current

Acceptable current rating with AC1	50 mA
------------------------------------	-------

Dimensions

Depth of installed product	68 mm
Width of installed product	17.5 mm

Power

Inrush power absorbed	2.4 VA
Total power loss under IN	2 W

Tripping

Performance voltage / Tripping at Ue	35 / 70 %
--------------------------------------	-----------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
Air humidity protection	95%
Storage/transport temperature	-40...80 °C