



MZ212



Over voltage release 230V AC

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U _e	230 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Microcut resistance	70 ms
Rated operational voltage in DC	0 V

Dimensions

Depth of installed product	68 mm
Height of installed product	87 mm
Width of installed product	17.5 mm

Power

Total power loss under I _N	0.7 W
---------------------------------------	-------

Tripping

Time of response when opening	7 s
Performance voltage / Tripping at U _e	110 / 180 %

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	10000

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C