



MZ521N

Surface mounting enclosure IP55 for motor starter

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Electric current

| | |
|---------------|------|
| Rated current | 25 A |
|---------------|------|

Dimensions

| | |
|----------------------------|--------|
| Depth of installed product | 125 mm |
|----------------------------|--------|

| | |
|-----------------------------|--------|
| Height of installed product | 158 mm |
|-----------------------------|--------|

| | |
|----------------------------|-------|
| Width of installed product | 80 mm |
|----------------------------|-------|

Cover, door

| | |
|------------------------------------|----|
| Identification of protection index | 55 |
|------------------------------------|----|

Materials

| | |
|----------|-----------------|
| Material | Polystyrol (PS) |
|----------|-----------------|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP55 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...55 °C |
|-----------------------|-------------|

| | |
|----------|--------|
| Altitude | 2000 m |
|----------|--------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -25...80 °C |
|-------------------------------|-------------|