



MZ529N

Under voltage release for motor starter 400V AC

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	400 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Rated insulation voltage	6000 V
DC control voltage	0 V
Command voltage AC	400 V
Rated operational voltage in DC	0 V

Dimensions

Depth of installed product	68 mm
Width of installed product	17.5 mm

Power

Inrush power absorbed	5 VA
Total power loss under IN	0.5 W
Power loss per pole at In	0.5 W

Tripping

Performance voltage / Tripping at Ue	35 / 70 %
--------------------------------------	-----------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...80 °C