



MZ529N

**Under voltage release for motor starter 400V AC**

**Technical properties**

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	400 V
Type of supply voltage	AC
Frequency	50 Hz

**Voltage**

Rated insulation voltage	6000 V
DC control voltage	0 V
Command voltage AC	400 V
Rated operational voltage in DC	0 V

**Dimensions**

Depth of installed product	68 mm
Width of installed product	17.5 mm

**Power**

Inrush power absorbed	5 VA
Total power loss under IN	0.5 W
Power loss per pole at In	0.5 W

**Tripping**

Performance voltage / Tripping at Ue	35 / 70 %
--------------------------------------	-----------

**Connection**

Connection cross-sect. flexible conductor	2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5mm <sup>2</sup>

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...80 °C