



MZ905

## Remote control auxiliary

### Technical properties

#### Configuration

Number of modules	3
-------------------	---

#### Main electrical features

Rated operational voltage U <sub>e</sub>	207 / 230 / 253 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	6 kV
Command voltage AC	207 / 230 / 253 V
Rated operational voltage in DC	230 V

#### Electric current

Acceptable current rating with AC1	5 A
Quiescent current	0 mA

#### Dimensions

Depth of installed product	71 mm
Height of installed product	83 mm
Width of installed product	54 mm

#### Power

Inrush power absorbed	1173 VA
Total power loss under I <sub>N</sub>	0.11 W

#### Installation, mounting

Tightening torque	1,7Nm;0,6Nm
-------------------	-------------

#### Connection

Connection cross-sect. flexible conductor	terminals 1 and 3 : 1 to 6mm <sup>2</sup> / terminals 2 up to 18 : 0,2 to 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	Terminals 1 and 2 : 1,5 / 10mm <sup>2</sup> - Terminals 2 up to 8 : 0,2 / 2,5mm <sup>2</sup>

#### Equipment

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

#### Safety

Dielectric properties distance between coil and contact	6Kv
<b>Use conditions</b>	
Operating temperature	-5...40 °C
<b>Identification</b>	
Aesthetic for B.G. Protection devices	FD