



MZ911

Auto reclosing remote control auxiliary

Technical properties

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	6 kV
Command voltage AC	207 / 230 / 253 V
Rated operational voltage in DC	230 V

Electric current

Acceptable current rating with AC1	5 A
Quiescent current	0 mA

Dimensions

Depth of installed product	71 mm
Height of installed product	83 mm
Width of installed product	54 mm

Installation, mounting

Tightening torque	1,7Nm;0,6Nm
-------------------	-------------

Connection

Connection cross-sect. flexible conductor	terminals 1 and 3 : 1 to 6mm ² / terminals 2 up to 18 : 0,2 to 2,5mm ²
Connection cross-sect. rigid cable	Terminals 1 and 2 : 1,5 / 10mm ² - Terminals 2 up to 8 : 0,2 / 2,5mm ²

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

Safety

Dielectric properties distance between coil and contact	6Kv
REACH conform	No
Halogen free	No

Use conditions

Operating temperature

-5...40 °C