



MZ913

**Auto reclosing remote control auxiliary**

**Technical properties**

**Configuration**

Number of modules	3
-------------------	---

**Main electrical features**

Rated operational voltage Ue	207 / 230 / 253 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	13 kV
Command voltage AC	207 / 230 / 253 V

**Electric current**

Acceptable current rating with AC1	5 A
Quiescent current	0 mA

**Dimensions**

Depth of installed product	71 mm
Height of installed product	83 mm
Width of installed product	52.5 mm

**Power**

Total power loss under IN	0.11 W
---------------------------	--------

**Installation, mounting**

Tightening torque	1,7Nm;0,6Nm
-------------------	-------------

**Connection**

Connection cross-sect. flexible conductor	terminals 1 and 3 : 1 to 6mm <sup>2</sup> / terminals 2 up to 18 : 0,2 to 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	Terminals 1 and 2 : 1,5 / 10mm <sup>2</sup> - Terminals 2 up to 8 : 0,2 / 2,5mm <sup>2</sup>

**Equipment**

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

**Safety**

Dielectric properties distance between coil and contact	6Kv
---	-----

**Use conditions**

