



MZ913

Auto reclosing remote control auxiliary

Technical properties

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	13 kV
Command voltage AC	207 / 230 / 253 V

Electric current

Acceptable current rating with AC1	5 A
Quiescent current	0 mA

Dimensions

Depth of installed product	71 mm
Height of installed product	83 mm
Width of installed product	52.5 mm

Power

Total power loss under IN	0.11 W
---------------------------	--------

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Dielectric properties distance between coil and contact	6Kv
---	-----

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------