



NRF0020A00

Empty module 20x22,5

Technical properties

Functions

Overvoltage protection	No
------------------------	----

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Type of supply voltage	AC
------------------------	----

Electric current

Rated current	16 A
---------------	------

Dimensions

Height of installed product	56.5 mm
-----------------------------	---------

Length	490 mm
--------	--------

Width of installed product	54 mm
----------------------------	-------

Materials

Colour	aluminium
--------	-----------

Material	Aluminium
----------	-----------

Material group	aluminium
----------------	-----------

Connection

Number of socket outlets Swiss standard type 15	0
---	---

Equipment

Number of connection cables	max. 2
-----------------------------	--------

Extension possible	No
--------------------	----

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature0...25 °C

Shape

ShapeSquare