



NRF0034D00

**module 4 outlets, 3 outlets locked, connector Wago**

#### Technical properties

##### Architecture

Connection system	Wago Winsta
-------------------	-------------

##### Functions

Overvoltage protection	No
------------------------	----

##### Main electrical features

Nominal voltage	250 V
Type of supply voltage	AC

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Height of installed product	55 mm
Length	375 mm
Width of installed product	55 mm

##### Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

##### Connection

Cross section connection cable	2.5 mm <sup>2</sup>
Number of HDMI sockets	0
Number of RJ45 CAT6 sockets	0
Number of USB sockets	0
Number of VGA sockets	0
Number of audio ports jack 3.5 mm	0

##### Cable

Length of the connecting cable	0 mm
--------------------------------	------

##### Equipment

Number of connection cables	max. 2
Number of appliances to build in	0
Number of USB interfaces	0
Number of household socket outlets	4
Extension possible	No

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Protection index IP	IP20
---------------------	------

**Shape**

Shape	Square
-------	--------