



NRF4204K00

module 4 outlets, 2 RJ45cat.6 UTP + 3m cable WAGO connect.

Technical properties

Architecture

Connection system	Wago Winsta
-------------------	-------------

Functions

Overvoltage protection	No
------------------------	----

Main electrical features

Nominal voltage	250 V
Type of supply voltage	AC

Electric current

Rated current	16 A
---------------	------

Dimensions

Height of installed product	55 mm
Length	265 mm
Width of installed product	55 mm

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Connection

Number of HDMI sockets	0
Number of RJ45 CAT6 sockets	2
Number of USB sockets	0
Number of VGA sockets	0
Number of audio ports jack 3.5 mm	0

Cable

Length of the connecting cable	3 m
--------------------------------	-----

Equipment

Number of connection cables	max. 1
Number of appliances to build in	0
Number of USB interfaces	0
Number of household socket outlets	4
Extension possible	No

Standards

Safety

Protection index IP

IP20

Shape

Shape

Square