



R25519010



**R 2551 White 9010 Intern.corner lid**

**Technical properties**

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

Product compatibility	LFS
-----------------------	-----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	40 mm
Length	50 mm
Trunking width	60 mm
Measure a	50 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
Material	Steel
Material group	steel
Type of surface treatment	Painted

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Protection index IP	IP30
---------------------	------

**Use conditions**

Operating temperature	-5...90 °C
-----------------------	------------