



R2551VERZ



**R 2551 Galv. Intern.corner lid**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility LFS

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 40 mm

Length 50 mm

Trunking width 60 mm

Measure a 50 mm

**Cover, door**

Lid with softlip -

**Materials**

Material Steel

Material group steel

Type of surface treatment Galvanised

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

Protection index IP IP30

**Use conditions**

Operating temperature -5...90 °C