



R25529010



R 2552 White 9010 Extern.corner lid

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LFS

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 40 mm

Length 50 mm

Trunking width 60 mm

Measure a 50 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material group steel

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK08

Use conditions

Operating temperature -5...90 °C