



R2555VERZ



R 2555 Galv. Flat corner

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LFS

Dimensions

Trunking height 40 mm

Trunking width 60 mm

Measure a 50 mm

Cover, door

Lid with softlip -

Materials

Material Steel

Type of surface treatment Galvanised

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Safety

Protection index IP IP30

Use conditions

Operating temperature -5...90 °C