


R2566VERZ



R 2566 Galv. T & X piece lid

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	40 mm
Length	200 mm
Trunking width	60 mm
Measure a	200 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	zinc coated
Material	Steel
Material group	steel
Type of surface treatment	Galvanised

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------