



R25739010



R 2573 White 9010 End cap

Technical properties

Architecture

Fixing mode Clamping and screwable

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 40 mm

Trunking width 60 mm

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material Steel

Material group steel

Type of surface treatment Painted

Standards

European directive RoHs voluntary compliance

Safety

Protection index IP IP30

Impact strength IK08

Use conditions

Operating temperature -5...90 °C