



R2582VERZ



R 2585 Galv Flat Corner

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LFS
-----------------------	-----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	60 mm
-----------------	-------

Length	50 mm
--------	-------

Trunking width	60 mm
----------------	-------

Measure a	50 mm
-----------	-------

Cover, door

Lid with softlip	-
------------------	---

Materials

Material	Steel
----------	-------

Material group	steel
----------------	-------

Type of surface treatment	Galvanised
---------------------------	------------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------