




R2646VERZ



**R 2646 Galv T & X Piece**

**Technical properties**

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Dimensions**

Trunking height	60 mm
Length	350 mm
Trunking width	100 mm
Measure a	350 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

Material	Steel
Material group	steel
Type of surface treatment	Galvanised

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Protection index IP	IP30
---------------------	------

**Use conditions**

Operating temperature	-5...90 °C
-----------------------	------------