



R26629010



Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	60 mm
Length	50 mm
Trunking width	100 mm
Measure a	50 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Material group	steel
Type of surface treatment	Painted

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------