



R2701VERZ



R 2701 Galv Internal Corner

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LFS

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 60 mm

Length 50 mm

Trunking width 150 mm

Measure a 50 mm

Cover, door

Lid with softlip -

Materials

Material Steel

Material group steel

Type of surface treatment Galvanised

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP30

Use conditions

Operating temperature -5...90 °C