



R2702VERZ



R 2702 Galv External Corner

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LFS
-----------------------	-----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	60 mm
Length	50 mm
Trunking width	150 mm
Measure a	50 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	zinc coated
Material	Steel
Material group	steel
Type of surface treatment	Galvanised

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature

-5...90 °C